










# Tray Cable Selection Guide

| Product Description   | Product  | Specificatio | Page Number |
|---|--|--------------|-------------|
| <b>X-Link® TC (Control)</b><br>90°C, 600 Volt<br>(XLPO/LSZH-XLPO)<br>Reduced Diameter<br>UL Listed, Type TC         |    | RSS-3-089    | T-1         |
| <b>X-Link® TC (Power)</b><br>90°C, 600 Volt<br>(XLPO/LSZH-XLPO)<br>Reduced Diameter<br>UL Listed, Type TC           |    | RSS-3-089    | T-3         |
| <b>X-Link® TC (Instrumentation)</b><br>90°C, 600 Volt<br>(XLPO/LSZH-XLPO)<br>Reduced Diameter<br>UL Listed, Type TC |    | RSS-3-089    | T-5         |
| <b>Firewall® III-C (Control)</b><br>90°C, 600 Volt<br>(XLPE/CSPE)<br>UL Listed, Type TC                             |    | RSS-3-022    | T-7         |
| <b>Firewall® III-C (Power)</b><br>90°C, 600 Volt<br>(XLPE/CSPE)<br>UL Listed, Type TC                               |  | RSS-3-022    | T-9         |
| <b>Firewall® III (Instrumentation)</b><br>90°C, 600 Volt<br>(XLPE/CSPE)<br>UL Listed, Type TC                       |  | RSS-3-021    | T-11        |
| <b>Pyrotrol® TC (Control)</b><br>90°C, 600 Volt<br>(XLPE/CPE)<br>UL Listed, Type TC                                 |  | RSS-3-103    | T-13        |
| <b>Pyrotrol® TC (Power)</b><br>90°C, 600 Volt<br>(XLPE/CPE)<br>UL Listed, Type TC                                   |  | RSS-3-103    | T-15        |
| <b>Pyrotrol® TC (Instrumentation)</b><br>90°C, 600 Volt<br>(XLPE/CPE)   |  | RSS-3-103    | T-17        |